


# Signal Cable assembly for RE3/3

2 pages , 1 one for each end of the cable

Note the cable length calculation for RE2/3 is NOT the same.



*for RE3/3*

**Chamber End**  
Enlever la gaine L= 150mm

Heat Shrink Tube  
Diam 10  
With internal Hot melt

Ground wire  
0.5mm<sup>2</sup>  
L= 300mm

L= 40mm

40 pin Scotch Flex  
(3M)

Cosse  
diam 6 x  
10mm

Ian Crotty  
20 Oct. 06

